



### The Standard - option polymer - pivoting

- Recommended for unsupported and gliding applications
- Well suited for tight installation conditions
- Strain relief with detachable tiwrap plates
- Variable traverse angle for flexible assembly
- The twistability of the E-Chain® and the option to assemble the mounting brackets on the fixed end and/or the moving end, enable various installation options


Moving end with bore  
(outer link) 2...3PZ(B)



2...4PZ(B) Fixed end  
with pin (inner link)




Possible installation conditions for assembled mounting brackets ► Order example "preassembled" below




### Option polymer - locking

- Recommended for unsupported and gliding applications
- Furthermore:
- At very high speed and/or acceleration
  - If space is limited for height (the  $H_F$  measurement)
  - The twistability of the E-Chain® and the option to assemble the mounting brackets on the fixed end and/or the moving end, enable various installation options

Moving end with bore  
(outer link) 2...1PZ(B)



2...2PZ(B) Fixed end  
with pin (inner link)



Possible installation conditions for assembled mounting brackets ► Order example "preassembled" below

2...3PZ(B) Standard! (pivoting)


2...1PZ(B) (locking)

Moving end

Standard! (pivoting) 2...4PZ(B)

(locking) 2...2PZ(B)

Fixed end



For E-Chain®	Part No. full set with tiwrap plate	Part No. tiwrap plate + 10 cable tiwraps	Part No. full set without tiwrap plate	Number of teeth	Dim. A [mm]
E200·Z200.05	2050. [ ] PZB	2050. [ ] PZBK1	2050. [ ] PZ	6	44
E200·Z200.2/35	2070. [ ] PZB	2070. [ ] PZBK1	2070. [ ] PZ	8	64
E200·Z200.2/50	2100. [ ] PZB	2100. [ ] PZBK1	2100. [ ] PZ	10	90

Please add the Part No. with the requested index - 34 for the pivoting configuration

e.g. 2050. [34] PZB or 12 for the locking configuration e.g. 2050. [12] PZB

For the preassembled mode please add the index [A1]...[A4] e.g. 2050. [34] PZB [A1]

### Dimensions and order configurations

Strain relief is possible on the moving end and/or the fixed end.

#### Part No. structure (pivoting)

2050. 34 PZB A1

A... must be indicated on preassembled configurations with assembled tiwrap plates

Full set pivoting = 34

Mounting brackets for selected chain type

#### Full set, for both ends:

2050. 34 PZB + tiwrap plate

#### Single-part order:

2050. 3 PZB + tiwrap plate

Mounting bracket with bore

2050. 4 PZB + tiwrap plate

Mounting bracket with pin

#### Part No. structure (locking)

2050. 12 PZB A1

A... must be indicated on preassembled configurations with assembled tiwrap plates

Full set locking = 12

Mounting brackets for selected chain type

#### Full set, for both ends:

2050. 12 PZB + tiwrap plate

#### Single-part order:

2050. 1 PZB + tiwrap plate

Mounting bracket with bore

2050. 2 PZB + tiwrap plate

Mounting bracket with pin

